

# Compression Terminal

By Burndy  
Catalog # YA34T4



Cu Compression Terminal, 1 Hole, 500 kcmil, 0.437" Hole Dia.

## Application

Wire Termination

## General

Connector Type	LONG BARREL
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810182505
UPC 12 Digit	7818101825055

## Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	1.50 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.38 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.52 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.71 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	25
-----------------------	----

## Product Assets

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA34T4-SPEC-EN | REV 8/2023