

YA35L45, Compression Terminal, 550 kcmil Cu, 1-Hole, 5/8" Stud, Standard Barrel

By Burndy
Catalog # YA35L45



Copper HYLUG™, Single hole W/ insp window, 550 kcmil, 5/8" stud, 21 index, Yellow, Tin Plated.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA35L45
Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	21
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810315262

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - D inch	1.33 in
Dimension - Height inch	2.62 in
Dimension - Hole Size fraction	5/8

Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.67 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.13 in
Dimension - Pad Width inch	1.65 in
Dimension - Strip Length inch	1-3/4
Dimension - Stud Size fraction	5/8
Dimension - Stud Size inch	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	550 KCMIL
Conductor - Copper Str Size Range	550 kcmil
Conductor - Material	COPPER
Conductor Size	550 KCMIL
Conductor Type	CODE

Certifications And Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - se209240-30](#)

[Specifications - YA35L45](#)
[Video - HYDENT Compression Terminal Overview Video](#)



©2024 Hubbell Incorporated. All rights reserved
BRDY-YA35L45-SPEC-EN | REV 10/2024