


Compression Terminal

By Burndy
Catalog # YA36A8

AL Terminal, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



Application

Wire Termination

General

Color Code	Black
Connector Type	DUAL RATED
Die Index	473
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Electro Tin plated
Material	ALUMINUM
Number of Holes	2
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A
UPC	781810129555
UPC 12 Digit	7818101295555

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.47 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - D inch	1.69 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.64 in
Dimension - N inch	0.69 in
Dimension - Outside Diameter inch	1.44 in
Dimension - Pad Width inch	1.97 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	600 KCMIL
Conductor - AL Str Size Range	600 kcmil
Conductor - Copper Str Size	600 KCMIL
Conductor - Copper Str Size Range	600 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	600 KCMIL
Conductor Type	CODE
Wire Size	600 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	2
Minimum Pack Quantity	2

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Aluminum Installation Instructions](#)
[Sales Drawings - SD073935-01](#)

Dimension - Stud Size fraction 3/8
Dimension - Thread Size 3/8
Dimension - Z inch 1.00 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA36A8-SPEC-EN | REV 8/2023