

Compression Terminal

By Burndy
Catalog # YA36TC12FXB

500 kcmil G, H, 444 DLO CU, One Hole, 1/2 Stud Size, Long Barrel, Bell End, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 20 or 299 Die Index.



Application

Wire Termination

General

Color Code	Brown
Connector Type	LONG BARREL
Die Index	20
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810039892
UPC 12 Digit	7818100398922

Dimensions

Dimension - B Length fraction	2-15/16 in
Dimension - B Length inch	2.95 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	129 mm
Dimension - Length Overall inch	5.09 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Pad Width inch	1.73 in
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2

Conductor Related

Conductor - Copper DLO Size	444 KCMIL
Conductor - Copper DLO Size Range	444.4 (1100/#24)
Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex H Size Range	444.4
Conductor - Copper Flex I Size	444.4
Conductor - Copper Flex I Size Range	444.4
Conductor - Copper Flex K Size	444.4
Conductor - Copper Flex K Size Range	444.4
Conductor - Copper Flex M Size	444.4
Conductor - Copper Flex M Size Range	444.4
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	FLEX
Wire Size	500 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2784

Dimension - Z inch 0.64 in
Physical Attribute - Tongue Angle Straight

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE208075](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA36TC12FXB-SPEC-EN | REV 8/2023