



# Compression Terminal

By Burndy  
Catalog # YA382TC38E10FX90

Cu Tubing Compression Terminal, 2 Holes W/O InspWindow, 535.3 kcmil(1325/#24)DLO (500 kcmil Flex), 3/8" Stud, 1.25" Spacing, 90 Deg Bent.



## Application

Wire Termination

## General

Color Code	Pink
Connector Type	LONG BARREL
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810476796
UPC 12 Digit	7818104767966

## Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Height inch	4.21 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.09 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	3-3/16
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.53 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

## Conductor Related

Conductor - Copper DLO Size	535 KCMIL
Conductor - Copper DLO Size Range	535 kcmil
Conductor - Copper Flex G Size	550 KCMIL
Conductor - Copper Flex G Size Range	550 kcmil
Conductor - Copper Flex H Size	500-550 KCMIL
Conductor - Copper Flex H Size Range	500 / 550 kcmil
Conductor - Copper Flex I Size	500-550 KCMIL
Conductor - Copper Flex I Size Range	500 / 550 kcmil
Conductor - Copper Flex K Size	500 KCMIL
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil
Conductor - Copper Str Size	500-550 KCMIL
Conductor - Copper Str Size Range	500 / 550 kcmil
Conductor - Material	COPPER
Conductor Size	500-550 KCMIL
Conductor Type	FLEX
Wire Size	500-550 KCMIL

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1850

Voltage - Maximum 35000  
Voltage Rating 35 kV

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..207814-01](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YA382TC38E10FX90-SPEC-EN | REV 5/2024