

Compression Terminal

By Burndy
Catalog # [YA38N45](#)

700 kcmil; 1 hole; 1/2" stud; long barrel; 45 angle.



Application

Wire Termination

General

Color Code	Pink
Connector Type	LONG BARREL
Die Index	400
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810315736
UPC 12 Digit	7818103157366

Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height inch	3.60 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.53 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	2-7/8
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	700 KCMIL
Conductor - Copper Str Size Range	700 kcmil
Conductor - Material	COPPER
Conductor Size	700 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - se209241-24](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA38N45-SPEC-EN | REV 8/2023