

YA39L6, Compression Terminal, 750 kcmil Cu, 1-Hole, 1/2" Stud, Standard Barrel



By Burndy
Catalog # [YA39L6](#)

750 kcmil CU, One Hole, 1/2 Stud Size, Standard Barrel,
Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90°
Up to 35kV, BLACK Color Code, 24 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA39L6
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	24
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG,TERMINALS
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810147276

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5

Dimension - D inch	1.08 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.41 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.91 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Carton Quantity 6
Minimum Pack Quantity 1

Product Assets

Catalogs - BURNDY Master Catalog - Section C - Compression Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD079848
Specifications - YA39L6
Video - HYDENT Compression Terminal Overview Video



A Hubbell brand