

Compression Terminal

By Burndy
Catalog # YA3CTC14

3 AWG CU, One Hole, 1/4 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, WHITE Color Code, 9 Die Index.



Application

Wire Termination

General

Color Code	White
Connector Type	LONG BARREL
Die Index	9
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Electro Tin Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810019610
UPC 12 Digit	7818100196100

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.64 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.23 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Navy Size	50 (19) Navy
Conductor - Copper Str Navy Size Range	50 (19) Navy
Conductor - Copper Str Size	3 AWG
Conductor - Copper Str Size Range	3 AWG
Conductor - Material	COPPER
Conductor Size	3 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SD..079849-02](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 1/4
Dimension - Z inch 0.33 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA3CTC14-SPEC-EN | REV 8/2023