

## YA402ENNTFX, 2-hole Long Barrel Connector, No Window, Narrow Tongue

By Burndy

Catalog # [YA402ENNTFX](#)

650 kcmil G, 646 DLO CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, No Window, Narrow Tongue, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 24 Die Index

### Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with a "chamfer" end opening at the wire entry to ensure smooth insertion of wire
- Long barrel allows for an increased number of crimps which will increase the mechanical strength of the connection
- Two hole tongue/tang is recommended when space permits as the 2-hole feature minimizes the terminations from loosening or rotatng under vibration, movement, or heat cycling

### General



\*Representative Image

Catalog Number	YA402ENNTFX
Type	Cable to Flat
UPC	621945619074

### Logistics

Carton Quantity	25
Pallet Quantity	1800

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50111162](#)
- [Specifications - YA402ENNTFX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)