



# YA402NTCFX, Compression Terminal, 650 kcmil G, 646 DLO, Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel

By Burndy  
Catalog # [YA402NTCFX](#)



Two hole Cu Tubing Compression Terminal with 6.95 inches long, Tin plated.

## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

## Application

Wire Termination

## General

Catalog Number	YA402NTCFX
Color Code	Black
Connector Type	LONG BARREL
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Electro Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810235706
UPC 12 Digit	7818102357066

## Dimensions

Dimension - B Length inch	2.94 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.02 in

Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	177 mm
Dimension - Length Overall inch	6.95 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.35 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	3
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	646 KCMIL
Conductor - Copper DLO Size Range	646 kcmil
Conductor - Copper Flex G Size	650 KCMIL
Conductor - Copper Flex G Size Range	650 kcmil
Conductor - Copper Flex H Size	650
Conductor - Copper Flex I Size	650
Conductor - Copper Flex K Size	650
Conductor - Copper Flex M Size	650
Conductor - Copper Str Size	650 KCMIL
Conductor - Copper Str Size Range	650 kcmil
Conductor - Material	COPPER
Conductor Size	650 KCMIL
Conductor Type	FLEX
Wire Size	650 KCMIL

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10066494](#)
- [Specifications - YA402NTCFX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-YA402NTCFX-SPEC-EN | REV 1/2025