

YA40LTC58FX, Compression Terminal, 650 kcmil G, 646 DLO, Cu., 1-Hole, 5/8" Stud, Standard Barrel



By Burndy
Catalog # [YA40LTC58FX](#)

650 kcmil G, 646 DLO CU, One Hole, 5/8 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 24 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA40LTC58FX
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810033302
UPC 12 Digit	7818100333022

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8

Dimension - Bolt Size inch	0.63
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.68 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.35 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	5/8
Dimension - Stud Size inch	5/8
Dimension - Thread Size	5/8 in
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	646 KCMIL
Conductor - Copper DLO Size Range	646 kcmil
Conductor - Copper Flex G Size	650 KCMIL
Conductor - Copper Flex G Size Range	650 kcmil
Conductor - Copper Flex H Size	650 Kcmil
Conductor - Copper Flex I Size	650 Kcmil
Conductor - Copper Flex K Size	650 Kcmil
Conductor - Copper Flex M Size	650 Kcmil
Conductor - Copper Str Size	650 KCMIL
Conductor - Copper Str Size Range	650 kcmil

Conductor - Material	COPPER
Conductor Size	650 KCMIL
Conductor Type	FLEX
Wire Size	650 KCMIL

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	3000

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - SE..208001-02](#)

[Specifications - YA40LTC58FX](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YA40LTC58FX-SPEC-EN | REV 1/2025