

YA44L2TC38, Compression Terminal, 1000 kcmil Cu, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel

By Burndy
Catalog # YA44L2TC38



Copper Compression Lug, 2 Hole w/ Inspection Window, 1000 kcmil, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin Plated.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA44L2TC38
Color Code	White
Connector Type	STANDARD BARREL
Die Index	27
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810020951
UPC 12 Digit	7818100209511

Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8

Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.74 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8 in
Dimension - Thread Size	3/8
Dimension - Z (inch)	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	1000 kcmil
Conductor - Copper Str Size	1000 KCMIL
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	COPPER
Conductor Size	1000 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	3
Minimum Pack Quantity	3

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD035209-15](#)
- [Specifications - YA44L2TC38](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand