



Compression Terminal

By Burndy
Catalog # YA44TC58FX

Copper Compression Lug, 1 Hole w/o Inspection Window, 750 Flex, 5/8" Stud, Long Barrel, Tin Plated.



Application

Wire Termination

General

Color Code	Yellow
Connector Type	LONG BARREL
Die Index	L115
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810235713
UPC 12 Digit	7818102357133

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - D inch	1.33 in
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	138 mm
Dimension - Length Overall inch	5.45 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.49 in
Dimension - Pad Width inch	2.19 in
Dimension - Stud Size fraction	5/8
Dimension - Thread Size	5/8 in
Dimension - Z inch	0.67 in

Conductor Related

Conductor - Copper DLO Size	777 KCMIL
Conductor - Copper DLO Size Range	777 kcmil
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper Flex G Size Range	750 kcmil
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex H Size Range	750 kcmil
Conductor - Copper Flex I Size	750 KCMIL
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex K Size	750
Conductor - Copper Flex K Size Range	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	3
Minimum Pack Quantity	3

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Physical Attribute - Tongue Angle Straight

[Video - HYDENT Compression Terminal Overview Video](#)

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA44TC58FX-SPEC-EN | REV 8/2023