

YA46, Compression Terminal, 1500 kcmil Cu, 1-Hole, 3/4" Stud, Long Barrel



By Burndy
Catalog # YA46

1500 kcmil CU, One Hole, 3/4 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GREEN Color Code, 31 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

General

Catalog Number	YA46
Color Code	Green
Connector Type	LONG BARREL
Die Index	29
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Electro-Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Electro-Tin Plated
UPC	781810037317
UPC 12 Digit	7818100373177

Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Hole Size inch	0.81 in
Dimension - Bolt Size fraction	3/4
Dimension - Bolt Size inch	0.75
Dimension - Hole Size fraction	3/4
Dimension - Hole Size inch	0.81

Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	153 mm
Dimension - Length Overall inch	6.04 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3-5/16 in
Dimension - Stud Size fraction	3/4
Dimension - Stud Size inch	3/4 in
Dimension - Thread Size	3/4 in
Dimension - Z (inch)	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	1500 Kcmil
Conductor - Copper Str Size	1500 KCMIL
Conductor - Copper Str Size Range	1500 kcmil
Conductor - Material	COPPER
Conductor Size	1250 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	3
Minimum Pack Quantity	3
Pallet Quantity	882

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD079849-10](#)
[Specifications - YA46](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA46-SPEC-EN | REV 10/2024