

Compression Terminal

By Burndy
Catalog # YA46L45

1500 kcmil CU, One Hole, 3/4 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, GREEN Color Code, 31 Die Index.



Application

Wire Termination

General

Color Code	Green
Connector Type	STANDARD BARREL
Die Index	31
Feature - Barrel Style	<ul style="list-style-type: none"> Chamfered Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810316962

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Bolt Size inch	0.75
Dimension - D inch	1.52 in
Dimension - Height inch	3.73 in
Dimension - Hole Size fraction	3/4
Dimension - Hole Size inch	0.81
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.75 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size fraction	3/4
Dimension - Stud Size inch	3/4
Dimension - Z (inch)	0.77 in
Physical Attribute - Tongue	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	1500 KCMIL
Conductor - Copper Str Size Range	1500 kcmil
Conductor - Material	COPPER
Conductor Size	1500 KCMIL
Conductor Type	CODE

Certifications And Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - se209240-37](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.