



YA48L, Compression Terminal, 2000 kcmil Cu, 1-Hole, 3/4" Stud, Standard Barrel

By Burndy
Catalog # [YA48L](#)



2000 kcmil CU, One Hole, 3/4 Stud Size, Standard Barrel,
Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90°
Up to 35kV, GREEN Color Code, 31 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA48L
Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	34
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810104996

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Bolt Size inch	0.75
Dimension - D inch	1.52 in
Dimension - Hole Size fraction	3/4
Dimension - Hole Size inch	0.81
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.19 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	2.13 in
Dimension - Pad Width inch	3.10 in
Dimension - Strip Length inch	2-3/8
Dimension - Stud Size fraction	3/4
Dimension - Stud Size inch	3/4
Dimension - Z (inch)	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	2000 KCMIL
Conductor - Copper Str Size Range	2000 kcmil
Conductor - Material	COPPER
Conductor Size	2000 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	740

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD079848](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA48L-SPEC-EN | REV 8/2024