

# YA4C2L90, Compression Terminal, #4 AWG Cu, 2-Hole, 1/4" Stud, .62" Spacing, Standard Barrel, 90 Degree

By Burndy  
Catalog # [YA4C2L90](#)



Two hole Cu Compression terminal, 4 AWG, 1/4" stud, 90 Degree Bent, Tin plated.

## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

## Application

Wire Termination

## General

Catalog Number	YA4C2L90
Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810317228
UPC 12 Digit	7818103172288

## Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25

Dimension - D inch	1.21 in
Dimension - Height inch	1.22 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - Inside Diameter inch	0.25 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.47 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.51 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	50
Minimum Pack Quantity	50

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se209512-08](#)
- [Specifications - YA4C2L90](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand