



Compression Terminal

By Burndy
Catalog # [YA4CN](#)

4 AWG CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GRAY Color Code, 8 or 346 Die Index.



General

Color Code	Gray
EU RoHS Indicator	Yes
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Long
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated

Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper Str Size Range	4 AWG
-----------------------------------	-------

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
----------------------	--------------

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - YA4CN_MODEL-IGES](#)
- [3D Models - YA4CN_MODEL-STEP](#)
- [3D Models - YA4CN_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD..079849-02](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA4CN-SPEC-EN | REV 8/2023