



YA5CN, Compression Terminal, #5 AWG Cu, 1-Hole, 1/2" Stud, Long Barrel

By Burndy
Catalog # YA5CN



5 AWG CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLUE Color Code, 7 or 374 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

General

Catalog Number	YA5CN
Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810317457
UPC 12 Digit	7818103174577

Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.56
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	68
Dimension - Length Overall inch	2.67
Dimension - N inch	0.63
Dimension - Outside Diameter inch	0.3
Dimension - Pad Width inch	0.83
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z (inch)	0.64
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	5 AWG
Conductor - Copper Str Navy Size	30 (19) Navy Size
Conductor - Copper Str Navy Size Range	30 (19) Navy Size Range
Conductor - Copper Str Size	5 AWG
Conductor - Copper Str Size Range	5 AWG
Conductor - Material	COPPER
Conductor Size	5 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..079849-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA5CN-SPEC-EN | REV 8/2024