

Compression Terminal

By Burndy
Catalog # YA6CL190

Copper HYLUG™, Short Barrel, Single hole /W/ insp window, #6 Str #6 Sol, #8 #10 stud, 7 or 374 index, Blue, Electro-Tin Plated, 90 Degree Bend.



Application

Wire Termination

General

Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810085479

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.54 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - D inch	0.49 in
Dimension - Height inch	0.94 in
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.72 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.42 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10:#8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

- [3D Models - YA6CL190_MODEL-IGES](#)
- [3D Models - YA6CL190_MODEL-STEP](#)
- [3D Models - YA6CL190_MODEL-PDF](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - se209240-03](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Z inch 0.27 in
Physical Attribute - Tongue Angle 90 Degree



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA6CL190-SPEC-EN | REV 8/2023