

YA6CL2TC516, Compression Terminal, #6 AWG Cu, 2-Hole, 5/16" Stud, 1" Spacing, Standard Barrel

By Burndy
Catalog # YA6CL2TC516



6 AWG CU, Two Hole, 5/16 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 or 374 Die Index.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

General

Catalog Number	YA6CL2TC516
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018774
UPC 12 Digit	7818100187744

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.54 in
Dimension - Bolt Hole Size inch	0.33 in

Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.78 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.52 in
Dimension - Strip Length inch	5/8 in
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16 in
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	

Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Carton Quantity 50
Minimum Pack Quantity 1

Product Assets

Catalogs - BURNDY Master Catalog - Section C - Compression Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD035209-04
Specifications - YA6CL2TC516
Video - HYDENT Compression Terminal Overview Video



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YA6CL2TC516-SPEC-EN | REV 10/2024