

YA8CL1NK, Compression Terminal, #8 AWG Cu, 1-Hole, 1/4" Stud, Standard Barrel, Nickel Plated

By Burndy
Catalog # [YA8CL1NK](#)



Cu Tubing Compression Terminal, 1 Hole W/InspWindow, #8 AWG #6 Sol. Code, 23 Navy, 600V - 35kV, 1/4" Stud, Nickel Plated.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA8CLINK
Color Code	Red
Connector Type	STANDARD BARREL
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Nickel Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810069547
UPC 12 Digit	7818100695477

Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.58 in
Dimension - Hole Size fraction	1/4

Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	8 AWG
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Flex I Size	"8 AWG"
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex M Size	"8 AWG"
Conductor - Copper Solid Size	6 Sol-8 Sol
Conductor - Copper Solid Size Range	8-6 Sol
Conductor - Copper Str Compact Size	"8 AWG"
Conductor - Copper Str Navy Size	23
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	COPPER

Conductor Size	8 AWG
Conductor Type	CODE/FLEX
Wire Size	8 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd079848-01](#)
- [Specifications - YA8CLINK](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand