

Compression Terminal

By Burndy
Catalog # YA8CL2TC14E145

8 AWG CU, Two Hole, 1/4 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Red Color Code, 49 Die Index.



Application

Wire Termination

General

Color Code	Red
Connector Type	STANDARD BARREL
Die Index	49
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810019108
UPC 12 Digit	7818100191088

Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	1.65 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.33 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper DLO Size	8 AWG
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Flex I Size	"8 AWG"
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex M Size	"8 AWG"
Conductor - Copper Flex M Size Range	8 AWG
Conductor - Copper Solid Size	6 Sol-8 Sol
Conductor - Copper Str Compact Size	"8 AWG"
Conductor - Copper Str Navy Size	23
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Str Size Range	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Solid Size Range	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - CopperWeld Str Size Range	8 A AWG-8 D AWG
Conductor - Material	COPPER
Conductor Size	8 AWG
Conductor Type	CODE/FLEX
Wire Size	8 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM

Dimension - Z inch 0.34 in
Physical Attribute - Tongue Angle 45 Degree

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV

UL Listed Yes

Logistics

Carton Quantity 50
Minimum Pack Quantity 50

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE..208119-01](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YA8CL2TC14E145-SPEC-EN | REV 8/2023