

YAD1010, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # YAD1010



Uninsulated Ring Terminal For 12 - 10 AWG.

Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For control wiring and other standard duty applications

General

Catalog Number	YAD1010
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Material	Copper
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810806388

Dimensions

Dimension - Bolt Size fraction #8 - #10

Conductor Related

Conductor Size 12 - 10 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094154](#)