

# Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [YAD1414](#)



Uninsulated Ring Terminal For 16 - 14 AWG.

## Application

For control wiring and other standard duty applications

## General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810806142
UPC 12 Digit	7818108061422

## Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.44 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094154](#)