



Uninsulated Ring Terminal For 3/0 AWG

By Burndy
Catalog # [YAD27M16E58](#)



Uninsulated Ring Terminal For 3/0 AWG.

Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

General

Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549506
UPC 12 Digit	7818105495066

Dimensions

Dimension - B Length inch	0.79 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.67 in
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.37 in
Dimension - Outside Diameter inch	0.79 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	5/8

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor Type	<ul style="list-style-type: none">CU C Str-SizeCU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	250
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAD36M20E34_LineArt](#)
[Sales Drawings - 50013616](#)



A proud member of the Hubbell Family.