

# YAD2CM20E34, Uninsulated Ring Terminal For 2 AWG, 1-Hole, 3/4" Stud

By Burndy  
Catalog # [YAD2CM20E34](#)



Uninsulated Ring Terminal For 2 AWG.

## Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

## Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

## General

Catalog Number	YAD2CM20E34
Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549186
UPC 12 Digit	7818105491866

## Dimensions

Dimension - B Length inch	0.47 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.80 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Outside Diameter inch	0.48 in
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	17/32
Dimension - Stud Size inch	3/4

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Flex-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	50

## Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section B - Small

Compression

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR\_YAD36M20E34\_LineArt

Sales Drawings - SE210981-02



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAD2CM20E34-SPEC-EN | REV 8/2024