



## YAE10N112BFBOX, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # YAE10N112BFBOX

Nylon Block Fork Terminal For 12 - 10 AWG.



### Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

### Application

Power Connector

### General

Catalog Number	YAE10N112BFBOX
Connector Type	Block Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAE-N
UPC	781810524442
UPC 12 Digit	7818105244422

### Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.29 in

### Electrical Ratings

Voltage - Maximum 600 V

### Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	50

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YAE18N104BFBOX\\_LineArt](#)  
[Sales Drawings - 50094183](#)



A Hubbell brand