



Nylon Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # [YAE10N11M](#)



Nylon Ring Terminal For 12 - 10 AWG (Tape Mounted).

General

Color Code	Yellow
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810028445
UPC 12 Digit	7818100284455

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	1.16 in
Dimension - Pad Width inch	0.38 in
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.30 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Reel

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50105268](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAE10N11M-SPEC-EN | REV 8/2023