



## YAE10N2BOX, Nylon Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YAE10N2BOX](#)



Nylon Ring Terminal For 12 - 10 AWG.

### Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

### Application

For Use On: 600 Volts Maximum, 105 Deg C Maximum

### General

Catalog Number	YAE10N2BOX
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Temperature Rating	105°C
Trade Name	INSULUG™
Type	YAE-N
UPC	781810023037
UPC 12 Digit	7818100230377

### Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - Hole Size fraction	32/97
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.39 in
Dimension - Pad Width inch	0.54 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	5/16
Dimension - Z (inch)	0.44 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section B - Small](#)

[Compression](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_YAE18NBOX\\_LineArt](#)

[Sales Drawings - 50094157](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAE10N2BOX-SPEC-EN | REV 8/2024