



Nylon Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAE10N83FBOX](#)



Nylon Fork Terminal For 12 - 10 AWG.

Application

Power Connector

General

Color Code	Yellow
Connector Type	Fork Terminal
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork Terminal
Plated	Y
Plating Type	Electro Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810533642
UPC 12 Digit	7818105336422

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.32 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094173](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAE10N83FBOX-SPEC-EN | REV 5/2024