



Nylon Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # YAE10NM



Nylon Ring Terminal For 12 - 10 AWG (Tape Mounted).

Application

Power Connector

General

Color Code	Yellow
Connector Type	Ring Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring Terminal
Plated	Y
Plating Type	Tin
Temperature Rating	105° C
Trade Name	INSULUG™
UPC	781810028650
UPC 12 Digit	7818100286500

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	#8-#10
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Reel

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50105268](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAE10NM-SPEC-EN | REV 8/2023