

YAE14Z2, Nylon Flanged Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAE14Z2](#)



Nylon Flanged Fork Terminal For 16 - 14 AWG.

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose

General

Catalog Number	YAE14Z2
Color Code	Blue
Connector Type	Flanged Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Electro Tin
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-Z, Flanged
UPC	781810804100
UPC 12 Digit	7818108041000

Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.146 in
Dimension - Length Overall inch	0.90 in

Dimension - N inch	0.15 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.25 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics


Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bulk
Pallet Quantity	99999

Product Assets

[3D Models - YAE14Z2_MODEL-IGES](#)
[3D Models - YAE14Z2_MODEL-PDF](#)
[3D Models - YAE14Z2_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_YAE18Z3_LineArt
Sales Drawings - 50094186
Specifications - YAE14Z2



©2024 Hubbell Incorporated. All rights reserved
BRDY-YAE14Z2-SPEC-EN | REV 10/2024