



Nylon Locking Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAE18N105LFBOX](#)



Nylon Locking Fork Terminal For 22 - 18 AWG.

Application

Power Connector

General

Color Code	Red
Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	Long Barrel
UPC	781810524602
UPC 12 Digit	7818105246022

Dimensions

Dimension - Bolt Size fraction	#6 - #8
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size fraction	#6;#8
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.32 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094178](#)
[Technical Solutions - BURNDY_YAE18N105LFBOX_Specsheet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAE18N105LFBOX-SPEC-EN | REV 1/2024