

YAE18N21M, Nylon Ring Terminal For 22 - 18 AWG (Tape Mounted)

By Burndy
Catalog # [YAE18N21M](#)



Nylon Ring Terminal For 22 - 18 AWG (Tape Mounted).

General

Catalog Number	YAE18N21M
Color Code	Red
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810028773
UPC 12 Digit	7818100287733

Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.89 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z (inch)	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	22 AWG - 16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486 Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
Packaging Type	Reel

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAE18N1M_LineArt](#)
[Sales Drawings - 50105268](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAE18N21M-SPEC-EN | REV 6/2024