




Nylon Flanged Fork Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22Z3](#)



Nylon Flanged Fork Terminal For 26 - 20 AWG.

Application

Power Connector

General

Color Code	Amber
Connector Type	Flanged Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAE-Z, Flanged
UPC	781810803820
UPC 12 Digit	7818108038200

Dimensions

Dimension - B Length fraction	3/23 in
Dimension - B Length inch	0.13 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.2 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	#6;#8
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Aircraft Size	AN 26;AN 22;AN 20
Conductor - Copper Str Size	20 AWG
Conductor - Copper Str Size Range	26 AWG - 20 AWG
Conductor Size	26 - 20 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bulk
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094186](#)
[Technical Solutions - BURNDY_YAE22Z3_Specsheet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAE22Z3-SPEC-EN | REV 1/2024

