



Compression Terminal

By Burndy
Catalog # [YAEBAFICNTNOEM](#)

Cu T-Type Battery Post Connector Terminal, #1 AWG, Green, 11 Index, 1-9/32 IN Strip Length, Polarity N.



Application

Battery Post Terminal

General

| | |
|---------------------------------------|----------------|
| Color Code | Green |
| Connector Type | BATTERY T-POST |
| Die Index | 11 |
| Finish Type | Tin-Plated |
| Installation Torque Recommended in-lb | 72 LBS/in |
| Material | COPPER |
| Plated | Y |
| Plating Type | Tin Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | OEM Terminals |
| UPC | 781810566237 |
| UPC 12 Digit | 7818105662377 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 60 mm |
| Dimension - Length Overall inch | 2.36 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-------------------------------------|-----------|
| Conductor - Copper DLO Size | 1 AWG |
| Conductor - Copper Flex G Size | 1 AWG |
| Conductor - Copper Flex H Size | 1 AWG |
| Conductor - Copper Flex I Size | 1 AWG |
| Conductor - Copper Flex K Size | 1 AWG |
| Conductor - Copper Flex M Size | 1 AWG |
| Conductor - Copper Str Compact Size | 1 AWG |
| Conductor - Copper Str Size | 1 AWG |
| Conductor - Copper Str Size Range | 1 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 1 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 1 AWG |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| Standards - RoHS Compliant | Yes |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 200 |
|-----------------------|-----|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50004536](#)
[SDS - Anti-Seize Lubricants SDS \(GHS\) \(2018-06\)](#)



