



## YAEBAF25NTNOEM, Cu T-Type Battery Post Connector Terminal, 1/0 AWG, Negative

By Burndy

Catalog # [YAEBAF25NTNOEM](#)



Cu T-Type Battery Post Connector Terminal, 1/0 AWG, Pink, 12 Index, 1-9/32 IN Strip Length, Polarity N.

### Application

Battery Post Terminal

### General

Catalog Number	YAEBAF25NTNOEM
Color Code	Pink
Connector Type	BATTERY T-POST
Die Index	12
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810547502
UPC 12 Digit	7818105475022

### Dimensions

Dimension - Inside Diameter inch	0.46 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	0.63 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Compact Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

### Logistics

Minimum Pack Quantity	200
-----------------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50004536](#)  
[SDS - Anti-Seize Lubricants SDS](#)  
[Specifications - YAEBAF25NTNOEM](#)



A Hubbell brand