

# Compression Terminal

By Burndy  
 Catalog # [YAEBAF27NTN](#)

Cu T Type Battery Post Connector Terminal, 3/0 AWG, 2.36" L, 1.97" W, Purple.



## Application

Battery Post Terminal

## General

Color Code	Orange
Connector Type	BATTERY T-POST
Die Index	14
Finish Type	Tin-Plated
Installation Torque Recommended in-lb	72 LBS/in
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562475
UPC 12 Digit	7818105624755

## Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-9/32
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Str Compact Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	10

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50004536](#)  
[SDS - Anti-Seize\\_Lubricants\\_GHS](#)



A proud member of the Hubbell Family.

BRDY-YAEBAF27NTN-SPEC-EN | REV 6/2023