



YAEBAF2CPTN, Cu T-Type Battery Post Connector Terminal, 2 AWG, Positive

By Burndy
Catalog # [YAEBAF2CPTN](#)

Cu T Type Battery Post Connector Terminal, #2 AWG, 2.36" L, 1.89" W, Green.



Application

Battery Post Terminal

General

Catalog Number	YAEBAF2CPTN
Color Code	Brown
Connector Type	BATTERY T-POST
Die Index	10
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563861
UPC 12 Digit	7818105638611

Dimensions

Dimension - Diameter Max Size inch	0.57 in
Dimension - Diameter Min Size inch	0.33 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-9/32
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Compact Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	10

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50004536](#)
[SDS - Anti-Seize Lubricants SDS](#)
[Specifications - YAEBAF2CPTN](#)

