

YAEBAS1CNTN, Straight Style Battery Post Terminal, 1 AWG, Negative

By Burndy
Catalog # YAEBAS1CNTN



Battery Post HYDENT Cu Terminals, #1 AWG, 2.30" L, 0.98" W, Pink, Wire Strip Length - 1-3/32" L.

Application

Battery Post Terminal

General

Catalog Number	YAEBAS1CNTN
Color Code	Green
Connector Type	BATTERY STRAIGHT POST
Die Index	11
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562574
UPC 12 Digit	7818105625744

Dimensions

Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.30 in
Dimension - Strip Length inch	1-3/32 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	1 AWG
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Str Compact Size	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG
Conductor Type	CODE/FLEX
Wire Size	1 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	10

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50004535](#)
[SDS - Anti-Seize Lubricants SDS](#)
[Specifications - YAEBAS1CNTN](#)



A Hubbell brand