



## YAEBAS26PTN, Straight Style Battery Post Terminal, 2/0 AWG, Positive

By Burndy  
Catalog # [YAEBAS26PTN](#)



Battery Post HYDENT Cu Terminals, 2/0 AWG, 2.36" L, 1.02" W,  
Orange, Wire Strip Length - 1-3/32" L.

### Application

Battery Post Terminal

### General

Catalog Number	YAEBAS26PTN
Color Code	Black
Connector Type	BATTERY STRAIGHT POST
Die Index	13
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562628
UPC 12 Digit	7818105626288

### Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-3/32 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Str Compact Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	10

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression  
Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50004535](#)  
[SDS - Anti-Seize Lubricants SDS](#)  
[Specifications - YAEBAS26PTN](#)



A Hubbell brand