



## YAEBAS27PTNOEM, Straight Style Battery Post Terminal, 3/0 AWG, Positive

By Burndy  
Catalog # YAEBAS27PTNOEM



Cu Battery Post Connector Terminal, 3/0 AWG, Orange, 14 Index, 1-3/32 IN Strip Length, Polarity P.

### Application

Battery Post Terminal

### General

Catalog Number	YAEBAS27PTNOEM
Color Code	Orange
Connector Type	BATTERY STRAIGHT POST
Die Index	14
Finish Type	Tin-Plated
Installation Torque	72 LBS/in
Recommended in-lb	
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563045
UPC 12 Digit	7818105630455

### Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Str Compact Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

### Logistics

Minimum Pack Quantity	150
-----------------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50004535](#)  
[SDS - Anti-Seize Lubricants SDS](#)  
[Specifications - YAEBAS27PTNOEM](#)



A Hubbell brand