

# Compression Terminal

By Burndy  
 Catalog # [YAEBAS6CNTNOEM](#)

Cu Battery Post Connector Terminal, #6 AWG, Blue, 7 Index, 1-3/32 IN Strip Length, Polarity N.



## Application

Battery Post Terminal

## General

Color Code	Blue
Connector Type	BATTERY STRAIGHT POST
Die Index	7
Finish Type	Tin-Plated
Installation Torque Recommended in-lb	72 LBS/in
Material	COPPER
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562970
UPC 12 Digit	7818105629700

## Dimensions

Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.30 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Str Compact Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50004535](#)  
[SDS - Anti-Seize\\_Lubricants\\_GHS](#)

