

Nylon Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAES10N13](#)



Nylon Ring Terminal For 12 - 10 AWG.

Application

For use on copper compression connections

General

Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES
UPC	781810805060
UPC 12 Digit	7818108050600

Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - G inch	0.33 in
Dimension - Hole Size inch	0.33 in
Dimension - Length Overall inch	1.32 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	5/16

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094155](#)
[Technical Solutions - BURNDY_YAES10N13_Specsheet](#)

