



## YAES10N57F, Nylon Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YAES10N57F](#)



Nylon Fork Terminal For 12 - 10 AWG.

### Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

### Application

Power Connector

### General

|                                      |               |
|--------------------------------------|---------------|
| Catalog Number                       | YAES10N57F    |
| Color Code                           | Yellow        |
| Connector Type                       | Fork Terminal |
| EU RoHS Indicator                    | Yes           |
| Feature - Barrel Style               | Shrouded      |
| Insulation                           | Y             |
| Insulation Type                      | Nylon         |
| Material                             | Copper        |
| Physical Attribute - Number of Holes | 1             |
| Physical Attribute - Tongue Type     | Fork          |
| Plated                               | Y             |
| Plating Type                         | Tin           |
| Sub Brand                            | INSULUG       |
| Trade Name                           | INSULUG™      |
| Type                                 | YAES-F        |
| UPC                                  | 781810805107  |
| UPC 12 Digit                         | 7818108051077 |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Bolt Size fraction    | 1/4      |
| Dimension - Hole Size fraction    | 10/37    |
| Dimension - Hole Size inch        | 0.27 in  |
| Dimension - Inside Diameter inch  | 0.22 in  |
| Dimension - Length Overall inch   | 1.21 in  |
| Dimension - N inch                | 0.25 in  |
| Dimension - Outside Diameter inch | 0.32 in  |
| Dimension - Pad Width inch        | 0.50 in  |
| Dimension - Strip Length inch     | 11/32 in |
| Dimension - Stud Size inch        | 1/4 in   |
| Dimension - Z (inch)              | 0.40 in  |

### Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

### Conductor Related

|                                   |               |
|-----------------------------------|---------------|
| Conductor - Copper Str Size       | 12 AWG;10 AWG |
| Conductor - Copper Str Size Range | 12 AWG-10 AWG |
| Conductor Size                    | 12 - 10 AWG   |
| Conductor Type                    | CU C Str-Size |

### Certifications And Compliance

|                                    |   |
|------------------------------------|---|
| Buy American Compliant             | Yes   |
| Certification - CSA Approved       | Yes   |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Industry Standard(s)               | <ul style="list-style-type: none"><li>• UL486</li><li>• Military Specified (Mil-Spec)</li></ul> |
| Standards - Industry Standards Met | UL486   |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes   |

## Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 500   |
| Minimum Pack Quantity | 500   |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small](#)  
[Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YAES10N56F\\_LineArt](#)  
[Sales Drawings - 50094172](#)  
[Specifications - YAES10N57F](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAES10N57F-SPEC-EN | REV 8/2024