

# Nylon Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [YAES14N54](#)



Nylon Ring Terminal For 16 - 14 AWG.

## Application

For use on copper compression connections

## General

Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES
UPC	781810804834
UPC 12 Digit	7818108048344

## Dimensions

Dimension - Bolt Size fraction	#12 - 1/4
Dimension - G inch	0.27 in
Dimension - Length Overall inch	1.08 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#12 - 1/4 in
Dimension - Width inch	0.46 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094155](#)  
[Technical Solutions - BURNDY\\_YAES14N54\\_Specsheet](#)

