

# Nylon Ring Terminal For 22 - 18 AWG

By Burndy  
Catalog # [YAES18N5](#)



Nylon Ring Terminal For 22 - 18 AWG.

## Application

For use on copper compression connections

## General

Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES
UPC	781810804919
UPC 12 Digit	7818108049199

## Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - G inch	0.4 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Stud Size inch	3/8 in
Dimension - Width inch	0.53 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>UL486</li> <li>Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094155](#)  
[Technical Solutions - BURNDY\\_YAES18N5\\_Specsheet](#)