

Nylon Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAES18N50F](#)



Nylon Fork Terminal For 22 - 18 AWG.

General

Color Code	Red
Connector Type	Fork Terminal
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810027196
UPC 12 Digit	7818100271966

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.03 in
Dimension - N inch	0.24 in
Dimension - Outside Diameter inch	0.24 in
Dimension - Pad Width inch	0.47 in
Dimension - Stud Size inch	1/4

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL486 Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> UL486 Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bulk
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094172](#)
[Technical Solutions - BURNDY_YAES18N50F_Specsheet](#)

