



YAEV10, Nylon Ring Terminal For 12 - 10 AWG

By Burndy

Catalog # [YAEV10](#)



Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Nylon Insulated, Short Barrel, Tin Plated, 600 Volts Max.

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Application

For High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

General

Catalog Number	YAEV10
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAEV, Heavy Duty
UPC	781810027806
UPC 14 Digit GTIN	00781810027806

Dimensions

Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in

Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.16 in
Dimension - N inch	0.19 in
Dimension - Outside Diameter inch	0.28 in
Dimension - P inch	0.09 in
Dimension - Pad Width inch	0.37 in
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.26 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Buy America(n) Qualified	<ul style="list-style-type: none">• TAA Compliant (All status valid till December 2024)• Buy America Compliant (All status valid till December 2024)
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus Industry Standard(s)	<ul style="list-style-type: none">• No• UL486• Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

- 360 Product View - BURN_YAEV10
- 3D Models - YAEV10_MODEL-PDF
- 3D Models - YAEV10_MODEL-IGES
- 3D Models - YAEV10_MODEL-STEP
- 3D Product View - BURN_YAEV10
- Catalogs - BURNDY Master Catalog - Section B - Small Terminals
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR_YAEV_LineArt
- Sales Drawings - 50094163
- Specifications - YAEV10

